

## P/N: 1196742

### Copyright

© 2017, FLIR Systems, Inc.

All rights reserved worldwide. Names and marks appearing herein are either registered trademarks or trademarks of FLIR Systems and/or its subsidiaries. All other trademarks, trade names or company names referenced herein are used for identification only and are the property of their respective owners.

### Document identity

Publ. No.: 1196742  
 Release:  
 Commit: 42932  
 Language: en-US  
 Modified: 2017-05-30  
 Formatted: 2017-05-31

### Website

<http://www.flir.com>

### Customer support

<http://support.flir.com>

### Disclaimer

Specifications subject to change without further notice. Camera models and accessories subject to regional market considerations. License procedures may apply. Products described herein may be subject to US Export Regulations. Please refer to [exportquestions@flir.com](mailto:exportquestions@flir.com) with any questions.



<b>General description</b>	
This wide angle lens is perfect for wide or tall targets or when working in crowded spaces.	
<b>Imaging and optical data</b>	
Field of view (FOV)	41.7° × 31.27°
Minimum focus distance	0.2 m (0.66 ft.)
Focal length	14.7 mm (0.58 in.)
Spatial resolution (IFOV)	2.38 mrad
F-number	1.5
<b>Shipping information</b>	
List of contents	<ul style="list-style-type: none"> <li>• Lens</li> <li>• Lens case</li> </ul>
EAN-13	7332558009130
UPC-12	845188009670
Country of origin	Sweden

### Compatible with the following products:

- N/A