

## P/N: 1196743

### Copyright

© 2017, FLIR Systems, Inc.

All rights reserved worldwide. Names and marks appearing herein are either registered trademarks or trademarks of FLIR Systems and/or its subsidiaries. All other trademarks, trade names or company names referenced herein are used for identification only and are the property of their respective owners.

### Document identity

Publ. No.: 1196743  
Release:  
Commit: 42932  
Language: en-US  
Modified: 2017-05-30  
Formatted: 2017-05-31

### Website


<http://www.flir.com>

### Customer support

<http://support.flir.com>

### Disclaimer

Specifications subject to change without further notice. Camera models and accessories subject to regional market considerations. License procedures may apply. Products described herein may be subject to US Export Regulations. Please refer to [exportquestions@flir.com](mailto:exportquestions@flir.com) with any questions.



General description	
This lens is ideal for small or distant targets such as overhead power lines.	
Imaging and optical data	
Field of view (FOV)	13.8° × 10.35°
Minimum focus distance	0.5 m (1.64 ft.)
Focal length	46.2 mm (1.82 in.)
Spatial resolution (IFOV)	0.76 mrad
F-number	1.5
Shipping information	
List of contents	<ul style="list-style-type: none"><li>• Lens</li><li>• Lens case</li></ul>
EAN-13	7332558009123
UPC-12	845188009663
Country of origin	Sweden

### Compatible with the following products:

- N/A