

P/N: T198511

Copyright

© 2017, FLIR Systems, Inc.

All rights reserved worldwide. Names and marks appearing herein are either registered trademarks or trademarks of FLIR Systems and/or its subsidiaries. All other trademarks, trade names or company names referenced herein are used for identification only and are the property of their respective owners.

Document identity

Publ. No.: T198511

Release:

Commit: 42932

Language: en-US

Modified: 2017-05-30

Formatted: 2017-05-31

Website

<http://www.flir.com>

Customer support

<http://support.flir.com>

Disclaimer

Specifications subject to change without further notice. Camera models and accessories subject to regional market considerations. License procedures may apply. Products described herein may be subject to US Export Regulations. Please refer to exportquestions@flir.com with any questions.



General description	
High capacity battery for the IR camera.	
Power system	
Battery type	Rechargeable Li ion battery
Battery voltage	7.2 V
Battery capacity	4.4 Ah at +20°C (+68°F)
Battery note	Approximate lithium content: 3.0 g
Charging system	In camera (AC adapter or 12 V from a vehicle) or 2-bay charger
Charging time	2.5 h to 95% capacity, charging status indicated by LED's
Charging temperature	0°C to +45°C (+32°F to +113°F)
Environmental data	
Battery storage temperature range	-40°C to +70°C (-40°F to +158°F)
Physical data	
Battery weight	0.24 kg (0.52 lb.)
Size (L x W x H)	141 x 47 x 28 mm (5.5 x 1.8 x 1.1 in.)
Shipping information	
Packaging, type	Cardboard box
Packaging, weight	0.324 kg (0.7 lb.)
Packaging, size	183 x 136 x 63 mm (7.2 x 5.4 x 2.5 in.)
EAN-13	7332558004364
UPC-12	845188004347
Country of origin	Sweden

Compatible with the following products:

- 44401-0201; FLIR GF300 14.5°
- 44402-0201; FLIR GF300 14.5° Fixed lens
- 44401-0202; FLIR GF300 24°
- 44402-0202; FLIR GF300 24° Fixed lens
- 59601-0101; FLIR GF304 14.5°
- 59602-0101; FLIR GF304 14.5° Fixed lens
- 59601-0102; FLIR GF304 24°
- 59602-0102; FLIR GF304 24° Fixed lens



Li-Ion Battery pack 7.4V 33Wh

P/N: T198511

© 2017, FLIR Systems, Inc.

#T198511; r./42932; en-US

- 44201-0101; FLIR GF306 14.5°
- 44202-0101; FLIR GF306 14.5° Fixed lens
- 44201-0102; FLIR GF306 24°
- 44202-0102; FLIR GF306 24° Fixed lens
- 44601-0101; FLIR GF309 14.5°
- 44602-0101; FLIR GF309 14.5° Fixed lens
- 44601-0102; FLIR GF309 24°
- 44602-0102; FLIR GF309 24° Fixed lens
- 44401-0101; FLIR GF320 14.5°
- 44402-0101; FLIR GF320 14.5° Fixed lens
- 44401-0102; FLIR GF320 24°
- 44402-0102; FLIR GF320 24° Fixed lens
- 57501-0102; FLIR GF335 24°
- 65702-0102; FLIR GF343 24° Fixed lens
- 59801-0101; FLIR GF346 14.5°
- 59802-0101; FLIR GF346 14.5° Fixed lens
- 59801-0102; FLIR GF346 24°
- 59802-0102; FLIR GF346 24° Fixed lens