

P/N: T911183

Copyright

© 2018, FLIR Systems, Inc.

All rights reserved worldwide. Names and marks appearing herein are either registered trademarks or trademarks of FLIR Systems and/or its subsidiaries. All other trademarks, trade names or company names referenced herein are used for identification only and are the property of their respective owners.

Document identity

Publ. No.: T911183

Release:

Commit: 42932

Language: en-US

Modified: 2017-05-30

Formatted: 2018-01-30

Website

<http://www.flir.com>

Customer support

<http://support.flir.com>

Disclaimer

Specifications subject to change without further notice. Camera models and accessories subject to regional market considerations. License procedures may apply. Products described herein may be subject to US Export Regulations. Please refer to exportquestions@flir.com with any questions.



General description	
Power supply, power over Ethernet (PoE) injector incl. multi plugs.	
Power system	
AC operation	Input: 100–240 V, 50–60 Hz
DC operation	Output: 56 VDC
Power	15.4 W
Physical data	
Size (L x W x H)	86x 50 x 33 mm (3.4 x 2.0 x 1.3 in.)
Color	Black
Shipping information	
List of contents	<ul style="list-style-type: none"> PoE injector EU plug UK plug US plug AU plug
EAN-13	7332558008683 4743254001787 (Estonia plant)
UPC-12	845188009205
Country of origin	Sweden

Compatible with the following products:

- 73309-0102; FLIR A35 f=9 mm with SC kit
- 83225-0101; FLIR A35 FOV 13 (60 Hz, ver. 2017)
- 83213-0102; FLIR A35 FOV 25 (60 Hz, ver. 2017)
- 83207-0102; FLIR A35 FOV 45 (60 Hz, ver. 2017)
- 83250-0101; FLIR A35 FOV 6.5 (60 Hz, ver. 2017)
- 83209-0102; FLIR A35 FOV 69 (30 Hz, ver. 2017)
- 73413-0102; FLIR A65 f=13 mm with SC kit (30 Hz)
- 73513-0102; FLIR A65 f=13 mm with SC kit (7.5 Hz)
- 75050-0101; FLIR A65 FOV 12.4 (30 Hz, ver. 2016)
- 75025-0101; FLIR A65 FOV 25 (30 Hz, ver. 2016)
- 75013-0101; FLIR A65 FOV 45 (30 Hz, ver. 2016)
- 75010-0101; FLIR A65 FOV 6.2 (30 Hz, ver. 2016)
- 75007-0101; FLIR A65 FOV 90 (30 Hz, ver. 2016)