

P/N: T911630ACC

Copyright

© 2019, FLIR Systems, Inc.

All rights reserved worldwide. Names and marks appearing herein are either registered trademarks or trademarks of FLIR Systems and/or its subsidiaries. All other trademarks, trade names or company names referenced herein are used for identification only and are the property of their respective owners.

Document identity

Publ. No.: T911630ACC

Commit: 49709

Language: en-US

Modified: 2018-05-14

Formatted: 2019-02-12

Website

<http://www.flir.com>

Customer support

<http://support.flir.com>

Disclaimer

Specifications subject to change without further notice. Camera models and accessories subject to regional market considerations. License procedures may apply. Products described herein may be subject to US Export Regulations. Please refer to exportquestions@flir.com with any questions.



General description	
Power supply, including multiple plugs, to charge the battery when it is inside the camera.	
Power system	
AC operation	100–240 VAC, 50/60 Hz, 5 VDC out
Power	3 A at 5 VDC
Physical data	
Size (L x W x H)	58 x 38 x 31 mm (2.3 x 1.5 x 1.2 in.)
Cable length	1.0 m (3.3 ft.)
Shipping information	
Packaging, type	Cardboard box
List of contents	<ul style="list-style-type: none"> • Power supply including cable • EU plug • UK plug • US plug • AU plug • Korea plug
Packaging, weight	0.180 kg (0.40 lb.)
Packaging, size	161 x 134 x 67 mm (6.3 x 5.3 x 2.6 in.)
EAN-13	4743254003163
UPC-12	845188014568
Country of origin	Estonia

Compatible with the following products:

- 85201-0102; FLIR GF77 25° CH4 (7–8.5 μm)
- 84502-0201; FLIR E53 24°
- 78501-0101; FLIR E75 14°
- 78502-0101; FLIR E75 24°
- 78504-0101; FLIR E75 24° + 14°
- 78506-0101; FLIR E75 24° + 14° & 42°
- 78505-0101; FLIR E75 24° + 42°
- 78503-0101; FLIR E75 42°
- 78507-0101; FLIR E75 42° + 14°
- 78501-0201; FLIR E85 14°
- 78502-0201; FLIR E85 24°
- 78504-0201; FLIR E85 24° + 14°
- 78506-0201; FLIR E85 24° + 14° & 42°
- 78505-0201; FLIR E85 24° + 42°



Power supply, 15 W/3 A

P/N: T911630ACC

© 2019, FLIR Systems, Inc.

#T911630ACC; r. 49709; en-US

- 78503-0201; FLIR E85 42°
- 78507-0201; FLIR E85 42° + 14°
- 78501-0301; FLIR E95 14°
- 78502-0301; FLIR E95 24°
- 78504-0301; FLIR E95 24° + 14°
- 78506-0301; FLIR E95 24° + 14° & 42°
- 78505-0301; FLIR E95 24° + 42°
- 78503-0301; FLIR E95 42°
- 79301-0101; FLIR T530 14°
- 79302-0101; FLIR T530 24°
- 79304-0101; FLIR T530 24° + 14°
- 79306-0101; FLIR T530 24° + 14° & 42°
- 79305-0101; FLIR T530 24° + 42°
- 79303-0101; FLIR T530 42°
- 79307-0101; FLIR T530 42° + 14°
- 79301-0201; FLIR T540 14°
- 79302-0201; FLIR T540 24°
- 79304-0201; FLIR T540 24° + 14°
- 79306-0201; FLIR T540 24° + 14° & 42°
- 79305-0201; FLIR T540 24° + 42°
- 79303-0201; FLIR T540 42°
- 79307-0201; FLIR T540 42° + 14°
- 82501-0201; FLIR T840 14°
- 82502-0201; FLIR T840 24°
- 82504-0201; FLIR T840 24° + 14°
- 82506-0201; FLIR T840 24° + 14° & 42°
- 82505-0201; FLIR T840 24° + 42°
- 82503-0201; FLIR T840 42°
- 82507-0201; FLIR T840 42° + 14°