



SECTION A-A

Konstr/Drawn J. MÄKINEN	Datum/Date 2015-03-06	Kontr/Check HAOS	Material EN AW-5052 or EN AW-5754			
Ändrad av/Modified by J. MÄKINEN	Ändrad/Modified 2015-05-21	Ytjämnhet/Roughness Ra            µm	Ytbehandling/Surface treatment			
Där ej annat anges/Unless otherwise stated Gen tol    ISO 2768-mK Utdrag ur/Excerpt from ISO 2768-m	Benämning/Denomination  Plate mounting front			Skala/Scale 1:1		Blad/Sheet 1(1)
0,5-6            ±0,1       Hålkårsradier (6)-30          ±0,2       Fillet radii (30)-120       ±0,3 (120)-400      ±0,5       Kanter brutna (400)-1000   ±0,8       Edges broken				Art.No.		Size A4
				Ritnr nr/Drawing No T128774		Rev A