



RoHS IP67

REV.	DESCRIPTION	DATE
A	ISSUE	Dec/23/2013
B	Modify the wire diagram.	Dec/25/2013
C	Modify M12 Pin Assignment.	Dec/25/2013
D	Modify cable length.	Dec/25/2013
D1	Correct key direction.	Jan/22/2014
E	Add note.	Mar/30/2014
F	Modify P/N.	Sep/25/2014
G	Modify connector to shielding type.	Nov/12/2014
G1	Change ring nut to shielding type.	Nov/25/2014



7	SHIELD	Brass, Nickel Plated.		1		Customer: FLIR			
6	RJ45 PLUG	RJ45 8P8C PLUG (shielding type).		1					
5	CABLE	CAT5E FTP 24AWG x 4 PAIR + AL/MY + Drain wire.	BLACK	1	WAC2B0026				
4	RING NUT	Brass, Nickel Plated.		1	M12S-RN-D985		UNIT: mm	TITLE M12 X-Coding Female Molded Cable Ass'y	
3	O-RING	Viton.	BLACK	1	M12-O-VK	SCALE	1:1		
2	CONTACT	Brass , Female pin ,6 u" Gold plated .		8	AASPF-1008-0.8	UNLESS OTHERWISE SPECIFIED TOLERANCES: X ± 0.25 XX ± 0.1 XXX ± 0.05 ANGLE ± 1°X		P/N: K129351004	
1	CONNECTOR	M12 X-coding Female connector insert. Nylon+GF.	BLACK	1	M12X-08F				
No.	PART NAME	DESCRIPTION	COLOR	Q'TY	REMARKS	REV.	SHEET	DWG.NO: T128390	DR. Stanley CH. ERIC AP.