

# Power and video cable, 2 m

## P/N: T129748ACC

### Copyright

© 2017, FLIR Systems, Inc.

All rights reserved worldwide. Names and marks appearing herein are either registered trademarks or trademarks of FLIR Systems and/or its subsidiaries. All other trademarks, trade names or company names referenced herein are used for identification only and are the property of their respective owners.

### Document identity

Publ. No.: T129748ACC

Release:

Commit: 42932

Language:

Modified: 2017-05-30

Formatted: 2017-05-31

### Website

<http://www.flir.com>

### Customer support

<http://support.flir.com>

### Disclaimer


Specifications subject to change without further notice. Camera models and accessories subject to regional market considerations. License procedures may apply. Products described herein may be subject to US Export Regulations. Please refer to [exportquestions@flir.com](mailto:exportquestions@flir.com) with any questions.



General description	
This cable is used to provide power to and composite video signals from FLIR KFx series cameras.	
Physical data	
Cable length	2.0 m (6.6 ft.)
Connector	<ul style="list-style-type: none"> <li>• Camera side: D38999/26FB35SN</li> <li>• Monitor side: 75 Ohm BNC connector, male</li> </ul>
Shipping information	
Packaging, type	Cardboard box
List of contents	Cable
Packaging, size	220 × 160 × 75 mm (8.7 × 6.3 × 3.0 in.)
EAN-13	7332558012284
UPC-12	845188013394
Country of origin	Sweden

### Compatible with the following products:

- 70901-0101; FLIR KF6, NTSC, Top Mounted, F
- 70901-0201; FLIR KF6, NTSC, Top Mounted, C
- 70901-0301; FLIR KF6, NTSC, Bottom Mounted, F
- 70901-0401; FLIR KF6, NTSC, Bottom Mounted, C
- 70901-0501; FLIR KF6, PAL, Top Mounted, F
- 70901-0601; FLIR KF6, PAL, Top Mounted, C
- 70901-0701; FLIR KF6, PAL, Bottom Mounted, F
- 70901-0801; FLIR KF6, PAL, Bottom Mounted, C




Märkt enl./ Marked acc. to: IS G009538  
 Text 1: "FLIR Art.nr."  
 Text 2: "Name"  
 Text 3: Made in Sweden  
 Text 4: "Manufacturers Name and S/N"

DETAIL A  
 SCALE 1 : 1

FLIR Art. nr.	Name	L
T129748	Power and Video Cable, 2m	2m

Det ihop lindade kablaget får ej överskrida dessa mått/  
 The coiled up cable may no be bigger then these measurements



Levererad ihop lindad i antistatisk ziplock påse/Delivered coiled up in antistatic zip lock bag

Tillverkad enl./Manufactured acc. to:  
 • IPCWHMA-A-620, Class 3 - Rev. A  
 • TF 614006335

Konstr/Drawn	Datum/Date	Kontr/Check	Material
M. Sternberg	2016-06-07	HEAH	-
Ändrad av/Modified by	Ändrad/Modified	Ytlämhet/Roughness	Ytbehandling/Surface treatment
M. Sternberg	2016-06-07	Ra - µm	-
Där ej annat anges/Unless otherwise stated Gen tol ± 3			
Hållskåp Fillet radii		MD	
Kanten brutna Edges broken		T129746	
<b>Power and Video Cable - Table Drawing</b>			