

## P/N: 20887-200

### Copyright

© 2017, FLIR Systems, Inc.

All rights reserved worldwide. Names and marks appearing herein are either registered trademarks or trademarks of FLIR Systems and/or its subsidiaries. All other trademarks, trade names or company names referenced herein are used for identification only and are the property of their respective owners.

### Document identity

Publ. No.: 20887-200

Release:

Commit: 42932

Language: en-US

Modified: 2017-05-30

Formatted: 2017-05-31

### Website


<http://www.flir.com>

### Customer support

<http://support.flir.com>

### Disclaimer

Specifications subject to change without further notice. Camera models and accessories subject to regional market considerations. License procedures may apply. Products described herein may be subject to US Export Regulations. Please refer to [exportquestions@flir.com](mailto:exportquestions@flir.com) with any questions.



<b>General description</b>	
This lens is suitable for the majority of applications.	
<b>Licensing and classification</b>	
License information	Interchangeable lens version of the ThermaCAM™ GasFindIR Class I, Div II, the ThermaCAM™ GasFindIR CO and the ThermaCAM™ GasFindIR HSX requires US Department of State License and will be subject to limitations on resale, except inside US. Allow a minimum of 90 days after application submittal for approval.
<b>Imaging and optical data</b>	
Field of view (FOV)	22° × 16°
Focal length	25 mm (0.98 in.)
Spatial resolution (IFOV)	1.2 mrad
F-number	2.3

### Compatible with the following products:

- 24059-251; ThermaCAM™ GasFindIR 25 mm lens Class I Div II PAL
- 24059-200; ThermaCAM™ GasFindIR 25 mm lens Class I Div II NTSC