

P/N: 4138205

Copyright

© 2018, FLIR Systems, Inc.

All rights reserved worldwide. Names and marks appearing herein are either registered trademarks or trademarks of FLIR Systems and/or its subsidiaries. All other trademarks, trade names or company names referenced herein are used for identification only and are the property of their respective owners.

Document identity

Publ. No.: 4138205

Release:

Commit: 44950

Language: en-US

Modified: 2017-09-13

Formatted: 2018-02-08

Website

<http://www.flir.com>

Customer support

<http://support.flir.com>

Disclaimer

Specifications subject to change without further notice. Camera models and accessories subject to regional market considerations. License procedures may apply. Products described herein may be subject to US Export Regulations. Please refer to exportquestions@flir.com with any questions.





Specifications	
Spectral band	3 - 5 microns
Focal length	13 mm
f /number	2.5
Average Transmission	> 86%
Distortion	< 4.5% on SC67XX
Focus range without vignetting	200mm to Infinity
Operating temperature	0 to +50°C
Storage temperature	-20 to +60°C
Weight	0.230 kg (0.51 lbs.)
Deg. Horizontal field of view (SC60XX/SC61XX)	63.2
Deg. Vertical field of view (SC60XX/SC61XX)	52.4
Deg. Diagonal field of view (SC60XX/SC61XX)	76.5
Deg. Horizontal field of view (SC67XX)	40.5
Deg. Vertical field of view (SC67XX)	32.9
Deg. Diagonal field of view (SC67XX)	50.6
Deg. Horizontal field of view (SC68XX)	63.2
Deg. Vertical field of view (SC68XX)	52.4
Deg. Diagonal field of view (SC68XX)	76.5
Interface	Three-Tab Bayonet

Compatible with the following products:

- 24048-201; FLIR SC6701
- 24048-203; FLIR SC6703

FLIR P/N 4138205 13mm LD f/2.5 3-5 microns SD Three Tab Bayonet



WEIGHT
(<305 g)
10.8 oz