

P/N: T129254

Copyright

© 2017, FLIR Systems, Inc.

All rights reserved worldwide. Names and marks appearing herein are either registered trademarks or trademarks of FLIR Systems and/or its subsidiaries. All other trademarks, trade names or company names referenced herein are used for identification only and are the property of their respective owners.

Document identity

Publ. No.: T129254
 Release:
 Commit: 42932
 Language: en-US
 Modified: 2017-05-30
 Formatted: 2017-05-31

Website


<http://www.flir.com>

Customer support

<http://support.flir.com>

Disclaimer

Specifications subject to change without further notice. Camera models and accessories subject to regional market considerations. License procedures may apply. Products described herein may be subject to US Export Regulations. Please refer to exportquestions@flir.com with any questions.



General description	
For high temperature applications the camera can be calibrated for high temperature ranges.	
Measurement	
Temperature range	<ul style="list-style-type: none"> • –20 to +120°C (–4 to +248°F) • 0 to +500°C (+32 to +932°F) • +300 to +2000°C (+572 to +3632°F)

Compatible with the following products:

- 48201-1001; FLIR A300
- 42701-1001; FLIR A300 (9 Hz)
- 48201-1101; FLIR A310
- 42701-1101; FLIR A310 (9 Hz)
- 48001-1101; FLIR A315
- 42901-1101; FLIR A315 (9 Hz)
- 48201-1201; FLIR A320 Tempscreen
- 42701-1201; FLIR A320 Tempscreen (9 Hz)
- 48001-1001; FLIR A325sc
- 71001-1103; FLIR A310 ex 25°
- 71001-1104; FLIR A310 ex 45°
- 61201-1003; FLIR A300f 25°
- 61201-1004; FLIR A300f 45°
- 61201-1102; FLIR A310f 15°
- 61201-1103; FLIR A310f 25°
- 61201-1104; FLIR A310f 45°
- 61201-1101; FLIR A310f 6°
- 61201-1105; FLIR A310f 90°
- 61201-1203; FLIR A315f 25°
- 61201-1204; FLIR A315f 45°
- 61201-1205; FLIR A315f 90°